

Flat suction cup (round)

SAFT-C 60 NBR-60 M10-AG

Part no.:10.01.01.11938

<https://www.schmalz.com/10.01.01.11938>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAFT-C > SAFT-C 60 NBR-60 M10-AG

Flat suction cup (round) for best dynamics on smooth, oily surfaces



Size: 60


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: M10-AG

Design Data



Attribute	Value
d	19 mm
dn	4 mm
Dk	40 mm
Dmax(S)	66 mm
Ds	63 mm
G1	M10-M
H	34 mm
H2	2 mm
LG1	11.50 mm
SW1	8 mm
Z (Stroke)	5.30 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	150 N
Lateral force	112 N
Lateral force (oily surface)	95 N
Volume	15 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SAFT-C 60 NBR-60 M10-AG

Part no.:10.01.01.11938

<https://www.schmalz.com/10.01.01.11938>

Size	60
Suction cup material	Nitrile rubber NBR
Weight	51.10 g
Number of folds	0
Product family	SAFT-C

Spare parts



SA-NIP N054 M10-AG DN400

Part no.:10.01.01.11942

Thread G1: M10-M

Material: Aluminum



REIB-SCHE 28x13.5 XNBR-45

Part no.:10.01.01.11943

External diameter D: 28 mm

Length L: 13.5 mm

Material: Perbunan XNBR

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SAFT-C 60 NBR-60 M10-AG

Part no...:10.01.01.11938

<https://www.schmalz.com/10.01.01.11938>



SAFT 60 NBR-60

Part no...:10.01.01.11937

Size: 60

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de