

Flat suction cup (round)

SHF 85 NK-45 M10x1.25-IG E

Part no.: 10.01.01.12209

<https://www.schmalz.com/10.01.01.12209>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SHF 85 NK-45 M10x1.25-IG E

Flat suction cup (round) for highly dynamic handling of wood



Size: 85


Thread G1: M10x1.25-F

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Type: E

Design Data



Attribute	Value
d2	62 mm
Dmax(S)	89 mm
Ds	85 mm
G1	M10x1.25-F
H	18.10 mm
LG1	10 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Size	85
Number of folds	0
Suction force (-600mbar)	198 N
Suction cup material	Natural Rubber NK
Volume	24.50 cm ³
Weight	81.80 g
Product family	SHF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de


Flat suction cup (round)

SHF 85 NK-45 M10x1.25-IG E

Part no.:10.01.01.12209

<https://www.schmalz.com/10.01.01.12209>

Accessories



RED-NIP G1/4-AG M10x1.25-AG AL

Part no.:10.01.01.12194

Thread G1: G1/4"-M

Material: Aluminum



SA-NIP N009 G1/4-IG DN440

Part no.:10.01.01.12192

Thread G1: G1/4"-F

Fitting length: 19.3 mm

Material: Aluminum



SIEB 14.5x1 MS-A2 0.103/0.15

Part no.:10.05.03.00023

External diameter D: 14.5 mm

Length L: 1 mm

Material: Brass / Stainless steel

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SHF 85 NK-45 M10x1.25-IG E

Part no...:10.01.01.12209

<https://www.schmalz.com/10.01.01.12209>



TVN G1/4-AG 9 N009

Part no...:10.05.10.00065

Thread G1: G1/4"-M

Thread G2: M10x1.25-M

Spring stroke Z: 9 mm

Nipple: N 009