

Suction plate (round)

SPK 110 MOS EPDM-15 G1/2-IG

Part no.:10.01.01.12062

<https://www.schmalz.com/10.01.01.12062>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Suction Plates SPK > SPK 110 MOS EPDM-15 G1/2-IG

Suction plate (round) for rough and structured surfaces



Size: 110


Material hardness [Shore A]: 15 Shore A

Material type: Foam rubber

Sealing material: EPDM

Connection: G1/2"-F

Design Data



Attribute	Value
d3	96 mm
Dmax(S)	130 mm
Ds	110 mm
G1	G1/2"-F
G2	G1/4"-F
H	25.50 mm
L2	36.50 mm
LG1	14.50 mm
LG2	14.50 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	471 N
Volume	67.40 cm ³
Curve radius (min) (convex)	500 mm
Hose diameter (rec.) d	12 mm
Size	110
Material hardness [Shore A]	15 Shore A
Weight	465 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPK 110 MOS EPDM-15 G1/2-IG

Part no.:10.01.01.12062

<https://www.schmalz.com/10.01.01.12062>

Number of folds

0

Product family

SPK

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



TV G1/4-AG 13

Part no.:10.05.10.00061

Thread G1: G1/4"-M

Thread G2: G1/8"-F

Spring stroke Z: 13 mm



SU 160

Part no.:10.01.01.12438

Size: 160

Clamping range: 150.0 ... 180.0 mm

Temperature resistance: 80 °C

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPK 110 MOS EPDM-15 G1/2-IG

Part no...:10.01.01.12062

<https://www.schmalz.com/10.01.01.12062>



DR-SPK 110 MOS EPDM-15

Part no...:10.01.01.12074

Size: 110

Material type: Foam rubber

Material hardness [Shore A]: 15 Shore A

Sealing material: EPDM



VRS-S G1/4-AG

Part no...:10.08.06.00048

Thread G1: G1/4"-M

Material: Brass

Surface: nickel plated



DR-SPK 110 MOS EPDM-15

Part no...:10.01.01.12074

Size: 110

Material type: Foam rubber

Material hardness [Shore A]: 15 Shore A

Sealing material: EPDM

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de