

Flat suction cup (round)

PFG 150 NBR-55 N010

Part no.:10.01.01.00333

<https://www.schmalz.com/10.01.01.00333>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 150 NBR-55 N010

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 150

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	7 mm
Dk	104.50 mm
Dmax(S)	158 mm
Ds	147.50 mm
H	31 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	842 N
Volume	164.71 cm ³
Curve radius (min) (convex)	300 mm
Size	150
Nipple family	N 010
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	411.30 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

PFG 150 NBR-55 N010

Part no.:10.01.01.00333

<https://www.schmalz.com/10.01.01.00333>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N010 G1/2-IG

Part no.:10.01.01.00796

Thread G1: G1/2"-F

Material: Aluminum



SU 160

Part no.:10.01.01.12438

Size: 160

Clamping range: 150.0 ... 180.0 mm

Temperature resistance: 80 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de