

## Flat suction cup (round)

PFG 10 SI-CO-55 N004

Part no.:10.01.01.00701

<https://www.schmalz.com/10.01.01.00701>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 10 SI-CO-55 N004

### Flat suction cup (round) for smooth or slightly rough surfaces




Size: 10

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

### Design Data



| Attribute  | Value    |
|------------|----------|
| d          | 4 mm     |
| d1         | 6 mm     |
| Dk         | 8.70 mm  |
| Dmax(S)    | 11.50 mm |
| Ds         | 10 mm    |
| H          | 7.50 mm  |
| H2         | 2 mm     |
| H3         | 4 mm     |
| Z (Stroke) | 1.40 mm  |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value                  |
|-----------------------------|------------------------|
| Suction force (-600mbar)    | 4 N                    |
| Volume                      | 0.15 cm <sup>3</sup>   |
| Curve radius (min) (convex) | 12.50 mm               |
| Size                        | 10                     |
| Nipple family               | N 004                  |
| Suction cup material        | Silicone SI conductive |
| Material hardness [Shore A] | 55 Shore A             |
| Weight                      | 0.30 g                 |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Flat suction cup (round)

PFG 10 SI-CO-55 N004

Part no.:10.01.01.00701

<https://www.schmalz.com/10.01.01.00701>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SA-NIP N004 G1/8-AG DN200

Part no.:10.01.01.03528

Thread G1: G1/8"-M

Length L1: 17 mm

Fitting length: 5 mm

Material: Aluminum



#### SA-NIP N004 G1/8-IG DN200

Part no.:10.01.01.03520

Thread G1: G1/8"-F

Length L1: 20 mm

Fitting length: 16 mm

Material: Aluminum



#### SA-NIP N004 M5-AG DN200

Part no.:10.01.01.03526

Thread G1: M5-M

Length L1: 13.5 mm

Fitting length: 5 mm

Material: Aluminum

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Flat suction cup (round)

PFG 10 SI-CO-55 N004

Part no...:10.01.01.00701

<https://www.schmalz.com/10.01.01.00701>



**SA-NIP N004 M5-IG DN200**

Part no...:10.01.01.03518

Thread G1: M5-F

Length L1: 14 mm

Fitting length: 10 mm

Material: Aluminum