

Bellows suction cups (round)

FSGA 33 NK-45 G1/4-AG DR

Part no.:10.01.06.01666

<https://www.schmalz.com/10.01.06.01666>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups with Sealing Ring > FSGA 33 NK-45 G1/4-AG DR

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 33

Suction cup material: Natural Rubber NK


Material hardness [Shore A]: 45 Shore A

Nipple material: Aluminum

Connection: G1/4"-M

Number of folds: 1.5

Design Data



Attribute	Value
d2	16 mm
dn	4.40 mm
Dmax(S)	38 mm
Ds	16 mm
G1	G1/4"-M
H	31 mm
LG1	11 mm
SW1	17 mm
Z (Stroke)	9 mm

Technical Data

Attribute	Value
Curve radius (min) (convex)	40 mm
Size	33
Number of folds	1.50
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Weight	15.60 g
Product family	FSGA

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cups (round)

FSGA 33 NK-45 G1/4-AG DR

Part no.:10.01.06.01666

<https://www.schmalz.com/10.01.06.01666>
