

Bellows suction cup HT1 (round)

SAB 80 HT1-60 G1/4-AG

Part no.: 10.01.06.03061

<https://www.schmalz.com/10.01.06.03061>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > Bellows Suction Cups SAB HT1 (1.5 Folds) > SAB 80 HT1-60 G1/4-AG

Bellows suction cup (round) for markless handling of workpieces



Size: 80

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

Number of folds: 1.5

Design Data



Attribute	Value
dn	6 mm
D1	63.60 mm
Dmax(S)	89 mm
Ds	81.10 mm
G1	G1/4"-M
H	49.90 mm
LG1	10 mm
SW1	22 mm
Z (Stroke)	22.10 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	135 N
Pull-off force	221 N
Lateral force	145 N
Lateral force (oily surface)	140 N
Volume	56.50 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Size	80

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cup HT1 (round)

SAB 80 HT1-60 G1/4-AG

Part no.:10.01.06.03061

<https://www.schmalz.com/10.01.06.03061>

Number of folds	1.50
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	72.10 g
Product family	SAB