

Bell suction cup (round)

SAG 60 NBR-60 M10-AG

Part no.:10.01.01.12297

<https://www.schmalz.com/10.01.01.12297>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAG > SAG 60 NBR-60 M10-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 60


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Steel

Connection: M10-AG

Design Data



Attribute	Value
dn	4 mm
Dmax(S)	70.50 mm
Ds	63.50 mm
G1	M10-M
H	43.20 mm
LG1	12 mm
SW1	22 mm
Z (Stroke)	10.60 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	122 N
Size	60
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Number of folds	0
Weight	54.40 g
Product family	SAG

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bell suction cup (round)

SAG 60 NBR-60 M10-AG

Part no.:10.01.01.12297

<https://www.schmalz.com/10.01.01.12297>
