

Bell suction cup (round)

SAXM 20 ED-85 G1/4-IG

Part no.: 10.01.19.00080

<https://www.schmalz.com/10.01.19.00080>

Home > Bell-Shaped Suction Cups SAXM > SAXM 20 ED-85 G1/4-IG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 20


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: G1/4-IG

Design Data



Attribute	Value
dn	5.10 mm
Dmax(S)	26 mm
Ds	21.80 mm
G1	G1/4"-F
H	33.70 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	20 N
Lateral force	15 N
Lateral force (oily surface)	20 N
Volume	1.55 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	5 mm
Size	20
Connection	G1/4"-F

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bell suction cup (round)

SAXM 20 ED-85 G1/4-IG

Part no.:10.01.19.00080

<https://www.schmalz.com/10.01.19.00080>

Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	14.20 g
Product family	SAXM

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC-A 045 G1/4-IG L


Part no.:10.01.06.02736

Connection geometry: 045

Thread G1: G1/4"-F

Fitting length: 17.2 mm

Shape: Self Locking



SAXM 20 ED-85 SC045

Part no.:10.01.19.00003

Size: 20

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bell suction cup (round)

SAXM 20 ED-85 G1/4-IG

Part no...:10.01.19.00080

<https://www.schmalz.com/10.01.19.00080>



SC-S 045 FDC-L

Part no...:10.01.06.02803

Shape: Frict elem with Self lock