

Bellows suction cup HT2 (round)

SAB 40 HT2-65 G1/4-AG

Part no.:10.01.06.02428

<https://www.schmalz.com/10.01.06.02428>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups SAB HT2 (1.5 Folds) > SAB 40 HT2-65 G1/4-AG

Bellows suction cup (round) for handling hot workpieces



Size: 40

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A


Temperature resistance: 200 °C

Nipple material: Aluminum

Connection: G1/4-AG

Number of folds: 1.5

Design Data



Attribute	Value
dn	4 mm
D1	32 mm
Dmax(S)	45 mm
Ds	40.10 mm
G1	G1/4"-M
H	29 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	10 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	38 N
Pull-off force	59 N
Lateral force	34 N
Volume	7 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Size	40
Connection	G1/4"-M

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cup HT2 (round)

SAB 40 HT2-65 G1/4-AG

Part no.:10.01.06.02428

<https://www.schmalz.com/10.01.06.02428>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Weight	23.10 g
Number of folds	1.50
Product family	SAB