

Bellows suction cup HT2 (round)

SAB 60 HT2-65 G3/8-IG

Part no...:10.01.06.03354

<https://www.schmalz.com/10.01.06.03354>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups SAB HT2 (1.5 Folds) > SAB 60 HT2-65 G3/8-IG

Bellows suction cup (round) for handling hot workpieces



Size: 60

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A


Temperature resistance: 200 °C

Nipple material: Aluminum

Connection: G3/8-IG

Number of folds: 1.5

Design Data



Attribute	Value
dn	6 mm
D1	49.50 mm
Dmax(S)	67 mm
Ds	61.20 mm
G1	G3/8"-F
H	41.30 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	14.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	82 N
Pull-off force	136 N
Lateral force	126 N
Volume	32 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	6 mm
Size	60
Connection	G3/8"-F

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cup HT2 (round)

SAB 60 HT2-65 G3/8-IG

Part no.:10.01.06.03354

<https://www.schmalz.com/10.01.06.03354>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Weight	51.50 g
Number of folds	1.50
Product family	SAB