

Flat suction cup (round)

SAF 40 HT2-65 G1/4-AG

Part no.:10.01.01.12353

<https://www.schmalz.com/10.01.01.12353>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > Flat Suction Cups SAF HT2 > SAF 40 HT2-65 G1/4-AG

Flat suction cup (round) for very dynamic handling



Size: 40

Suction cup material: High temperature material HT2


Material hardness [Shore A]: 65 Shore A

Temperature resistance: 200 °C

Nipple material: Aluminum

Connection: G1/4-AG

Design Data



Attribute	Value
dn	4 mm
Ds	41 mm
Dmax(S)	46 mm
G1	G1/4"-M
H	22 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Number of folds	0
Size	40
Suction force (-600mbar)	69 N
Temperature resistance	200 °C
Product family	SAF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SAF 40 HT2-65 G1/4-AG

Part no.:10.01.01.12353

<https://www.schmalz.com/10.01.01.12353>

Accessories



SU 40

Part no.:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C