

Flat suction cup (round)

SAF 60 HT2-65 G1/4-IG

Part no.:10.01.01.12360

<https://www.schmalz.com/10.01.01.12360>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > Flat Suction Cups SAF HT2 > SAF 60 HT2-65 G1/4-IG

Flat suction cup (round) for very dynamic handling



Size: 60

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A

Temperature resistance: 200 °C

Nipple material: Nickel plated

Connection: G1/4-IG

Design Data



Attribute	Value
dn	6 mm
Ds	60.60 mm
Dmax(S)	67 mm
G1	G1/4"-F
H	36 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	6 mm

Technical Data

Attribute	Value
Number of folds	0
Size	60
Suction force (-600mbar)	150 N
Temperature resistance	200 °C
Product family	SAF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SAF 60 HT2-65 G1/4-IG

Part no.:10.01.01.12360

<https://www.schmalz.com/10.01.01.12360>

Accessories



SU 60

Part no.:10.01.01.13585

Size: 60

Clamping range: 60.0 ... 70.0 mm

Temperature resistance: 80 °C