

Flat suction cup (round)

SAF 30 HT2-65 G3/8-IG

Part no.:10.01.01.12350

<https://www.schmalz.com/10.01.01.12350>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > Flat Suction Cups SAF HT2 > SAF 30 HT2-65 G3/8-IG

Flat suction cup (round) for very dynamic handling



Size: 30

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A

Temperature resistance: 200 °C

Nipple material: Nickel plated

Connection: G3/8-IG

Design Data



Attribute	Value
dn	4 mm
Ds	31 mm
Dmax(S)	34 mm
G1	G3/8"-F
H	36 mm
LG1	9 mm
SW1	22 mm
Z (Stroke)	3 mm

Technical Data

Attribute	Value
Number of folds	0
Size	30
Suction force (-600mbar)	38 N
Temperature resistance	200 °C
Product family	SAF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SAF 30 HT2-65 G3/8-IG

Part no.:10.01.01.12350

<https://www.schmalz.com/10.01.01.12350>

Accessories



SU 30

Part no.:10.01.01.12889

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C