

Suction plate (round)

SPU 250 NBR-55 G1/2-IG

Part no.:10.01.01.01097

<https://www.schmalz.com/10.01.01.01097>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Wood > Suction Plates
SPU > SPU 250 NBR-55 G1/2-IG

Suction plate (round), universal, for smooth and slightly rough surfaces




Size: 250

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Connection: G1/2"-F

Design Data



Attribute	Value
d	34 mm
d2	203 mm
d3	178 mm
Dmax(S)	263 mm
Ds	252 mm
G1	G1/2"-F
G2	G1/2"-F
H	25 mm
H1	26.50 mm
L2	76 mm
LG1	13.50 mm
LG2	15 mm
Z (Stroke)	6.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	2650 N
Suction force d2	1940 N
Volume	370 cm ³

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPU 250 NBR-55 G1/2-IG

Part no.:10.01.01.01097

<https://www.schmalz.com/10.01.01.01097>

Curve radius (min) (convex)	2200 mm
Hose diameter (rec.) d	12 mm
Size	250
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	1360 g
Number of folds	0
Product family	SPU

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 280

Part no.:10.01.01.12485

Size: 280

Clamping range: 270.0 ... 300.0 mm

Temperature resistance: 80 °C

Spare parts



DR-SPU 250 NBR-55

Part no.:10.01.01.01094

Size: 250

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPU 250 NBR-55 G1/2-IG

Part no...:10.01.01.01097

<https://www.schmalz.com/10.01.01.01097>
