

Bellows suction cup HT2 (round)

SAB 22 HT2-65 G3/8-IG

Part no.: 10.01.06.02421

<https://www.schmalz.com/10.01.06.02421>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups SAB HT2 (1.5 Folds) > SAB 22 HT2-65 G3/8-IG

Bellows suction cup (round) for handling hot workpieces



Size: 22

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A


Temperature resistance: 200 °C

Nipple material: Nickel plated

Connection: G3/8-IG

Number of folds: 1.5

Design Data



Attribute	Value
dn	3.50 mm
D1	22 mm
Dmax(S)	24 mm
Ds	20.60 mm
G1	G3/8"-F
H	41 mm
LG1	9.50 mm
SW1	22 mm
Z (Stroke)	5.80 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	16 N
Pull-off force	24 N
Lateral force	17 N
Volume	1.50 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	22
Connection	G3/8"-F

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cup HT2 (round)

SAB 22 HT2-65 G3/8-IG

Part no.:10.01.06.02421

<https://www.schmalz.com/10.01.06.02421>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Weight	42.80 g
Number of folds	1.50
Product family	SAB