

Bellows suction cup (round)

SPB4 30 SI-55 G1/4-IG

Part no.:10.01.06.03524

<https://www.schmalz.com/10.01.06.03524>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups SPB4 (4.5 Folds) > SPB4 30 SI-55 G1/4-IG

Bellows suction cup (round) for very uneven workpieces



Size: 30


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Thread G1: G1/4"-F

Number of folds: 4.5

Design Data



Attribute	Value
d2	17 mm
dn	11 mm
Dmax(S)	31.50 mm
Ds	30.20 mm
G1	G1/4"-F
H	69.50 mm
LG1	12 mm
SW1	22 mm
Z (Stroke)	20 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	16 N
Pull-off force	22 N
Volume	15.61 cm ³
Hose diameter (rec.) d	9 mm
Number of folds	4.50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Size	30

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cup (round)

SPB4 30 SI-55 G1/4-IG

Part no.: 10.01.06.03524

<https://www.schmalz.com/10.01.06.03524>

Weight	27.50 g
Product family	SPB4

Accessories



SIEB 17x0.8 MS-A2 103 0.103/0.07

Part no.: 10.07.01.00320

External diameter D: 17 mm

Length L: 0.8 mm

Material: Brass / Stainless steel

Filter pore size: 103 µm



SSB 16-27 ST-VZ

Part no.: 10.07.10.00002

Clamping range: 16.0 ... 27.0 mm

Material: Steel

Surface: galvanised



SPI 24 PE SPB4-30

Part no.: 10.01.06.02855

Size: 24

Material: Polyethylene

Use: SPB4-30

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cup (round)

SPB4 30 SI-55 G1/4-IG

Part no...:10.01.06.03524

<https://www.schmalz.com/10.01.06.03524>



SPSE 30

Part no...:10.01.06.02953

Size: 30

Spare parts



SC 080 G1/4-AG

Part no...:10.01.06.03268

Connection geometry: 080

Vacuum connection: G1/4"-M

Length L1: 32 mm

Fitting length: 7.5 mm

Nominal diameter dn: 8 mm



SC 080 G1/4-IG

Part no...:10.01.06.03271

Connection geometry: 080

Vacuum connection: G1/4"-F

Length L1: 32 mm

Fitting length: 17.5 mm

Nominal diameter dn: 11 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cup (round)

SPB4 30 SI-55 G1/4-IG

Part no...:10.01.06.03524

<https://www.schmalz.com/10.01.06.03524>



SPB4 30 SI-55 SC080

Part no...:10.01.06.02589

Size: 30

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 4.5

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de