

Flat suction cup (round)

SPF 25 ED-65 G1/8-IG

Part no.: 10.01.01.13243

<https://www.schmalz.com/10.01.01.13243>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Flat Suction Cups SPF > SPF 25 ED-65 G1/8-IG

Flat suction cup (round) for dynamic handling of cardboard and rigid packaging




Size: 25

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/8"-F

Design Data



Attribute	Value
dn	4.10 mm
Dmax(S)	28 mm
Ds	26.40 mm
G1	G1/8"-F
H	25 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	22.70 N
Pull-off force	27.10 N
Lateral force	17 N
Volume	1.70 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	4 mm
Size	25

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SPF 25 ED-65 G1/8-IG

Part no.:10.01.01.13243

<https://www.schmalz.com/10.01.01.13243>

Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	7.30 g
Product family	SPF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SIEB 11x1 MS-A2 280 0.28/0.16

Part no.:10.07.01.00309

External diameter D: 11 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm



SU 25

Part no.:10.01.01.13584

Size: 25

Clamping range: 25.0 ... 30.0 mm

Temperature resistance: 80 °C

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SPF 25 ED-65 G1/8-IG

Part no...:10.01.01.13243

<https://www.schmalz.com/10.01.01.13243>



SC 040 G1/8-IG

Part no...:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm



SPF 25 ED-65 SC040

Part no...:10.01.01.12371

Size: 25

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Height H: 11 mm