

Flat suction cup (round)

SGPN 40 NK-40 G1/4-IG

Part no.:10.01.01.00794

<https://www.schmalz.com/10.01.01.00794>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 40 NK-40 G1/4-IG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 40


Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Nipple material: Aluminum

Vacuum connection: G1/4"-F

Design Data



Attribute	Value
dn	5 mm
Dmax(S)	42 mm
Ds	40 mm
G1	G1/4"-F
H	35.60 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	2.30 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	33 N
Volume	3.80 cm ³
Hose diameter (rec.) d	4 mm
Size	40
Number of folds	0
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	40 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SGPN 40 NK-40 G1/4-IG

Part no.:10.01.01.00794

<https://www.schmalz.com/10.01.01.00794>

Weight	13.10 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N035 G1/4-IG DN550

Part no.:10.01.01.00821

Thread G1: G1/4"-F

Fitting length: 15 mm

Material: Aluminum



SGP 40 NK-40 N035

Part no.:10.01.01.00789

Size: 40

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de