

Flat suction pad (round)

SFF 10 EPDM-45 M5-AG

Part no.: 10.01.01.14260

<https://www.schmalz.com/10.01.01.14260>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFF 10 EPDM-45 M5-AG

Flat suction cup (round) for dynamic handling of thin and flexible workpieces




Size: 10

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Design Data



Attribute	Value
Dmax(S)	11 mm
Ds	10 mm
dn	1.80 mm
G1	M5-AG
LG1	4.70 mm
H	15.40 mm
SW1	8 mm
Z (Stroke)	0.70 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	2.70 N
Volume	0.25 cm ³
Size	10
Number of folds	0
Suction cup material	EPDM
Material hardness [Shore A]	45 Shore A
Weight	1.60 g
Product family	SFF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction pad (round)

SFF 10 EPDM-45 M5-AG

Part no.:10.01.01.14260

<https://www.schmalz.com/10.01.01.14260>

Spare parts



SFF 10 EPDM-45 SC030

Part no.:10.01.01.14044

Size: 10

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Number of folds: 0



SC 030 M5-AG

Part no.:10.01.06.02802

Connection geometry: 030

Connection: M5-M

Length L1: 15.5 mm

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de