

Check valve

SVN G1/4-AG M10x1.25-AG N009

Part no.:10.05.03.00060

<https://www.schmalz.com/10.05.03.00060>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Check Valves and Flow Restrictors > Check Valves SVN > SVN G1/4-AG M10x1.25-AG N009

Connection nipple with integrated check valve




Thread G1: G1/4"-M

Thread G2: M10x1.25-M

Spanner size SW1: 17 mm

Nipple family: N009

Design Data



Attribute	Value
G1	G1/4"-M
G2	M10x1.25-M
L	5 mm
LG1	10 mm
LG2	10 mm
SW1	17 mm

Technical Data

Attribute	Value
Evacuation rate for pu = -0,3 bar	2.30 m³/h
Evacuation rate for pu = -0,3 bar	38.30 l/min
Evacuation rate for pu = -0,6 bar	3.30 m³/h
Evacuation rate for pu = -0,6 bar	55 l/min
Flow rate max.	27 m³/h
Flow rate max. vacuum	450 l/min
Weight	10 g
Product family	SVN

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Check valve

SVN G1/4-AG M10x1.25-AG N009

Part no.:10.05.03.00060

<https://www.schmalz.com/10.05.03.00060>
