

Flat suction cup (round)


PFG 30 PU-55 N007

Osanro.:10.01.01.00054

<https://www.schmalz.com/10.01.01.00054>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > PFG 30 PU-55 N007

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 30

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A

Suunnitteludata



Attribuutti	Arvo
d	6 mm
d1	11 mm
Dk	15,10 mm
Dmax(S)	31,50 mm
Ds	28,80 mm
H	12 mm
H2	7 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	34 N
Volume	1,56 cm ³
Curve radius (min) (convex)	40 mm
Size	30
Nipple family	N 007
Suction cup material	Polyurethane PU
Material hardness [Shore A]	55 Shore A
Weight	3 g

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

PFG 30 PU-55 N007

Osanro.:10.01.01.00054

<https://www.schmalz.com/10.01.01.00054>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



SA-NIP N007 G1/8-AG DN240

Osanro.:10.01.01.03531

Nipple family: N 007

Thread G1: G1/8"-M

Length L1: 21 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2,4 mm

Material: Aluminum

Spanner size SW2: 4 mm



SA-NIP N007 G1/8-IG DN350

Osanro.:10.01.01.03523

Nipple family: N 007

Thread G1: G1/8"-F

Length L1: 24,5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

Spanner size SW2: 4 mm



SU 30

Osanro.:10.01.01.12889

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C

Flat suction cup (round)

PFG 30 PU-55 N007

Osanro.:10.01.01.00054

<https://www.schmalz.com/10.01.01.00054>
