

Flat suction cup (round)

PFG 15 HT1-60 N005

Osanro.:10.01.01.11162

<https://www.schmalz.com/10.01.01.11162>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > PFG 15 HT1-60 N005

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 15

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking

Suunnitteludata



Attribuutti

Arvo

d	4,50 mm
d1	7,80 mm
Dk	12,20 mm
Dmax(S)	17,50 mm
Ds	15 mm
H	8 mm
H2	2,60 mm
Z (Stroke)	1,90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	9 N
Volume	0,43 cm ³
Curve radius (min) (convex)	12,50 mm
Size	15
Nipple family	N 005
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	0,70 g

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

PFG 15 HT1-60 N005

Osanro.:10.01.01.11162

<https://www.schmalz.com/10.01.01.11162>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



SA-NIP N005 G1/8-AG DN200

Osanro.:10.01.01.03529

Nipple family: N 005

Thread G1: G1/8"-M

Length L1: 17,5 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2 mm

Material: Aluminum



SA-NIP N005 G1/8-IG DN200

Osanro.:10.01.01.03521

Nipple family: N 005

Thread G1: G1/8"-F

Length L1: 20,5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 2 mm

Material: Aluminum