

Vacuum hose (meter)

VSL 6-4 PU MI-TR

Osanro.:10.07.09.00002

<https://www.schmalz.com/10.07.09.00002>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Erityinen tarttuja > Neulan tarttuja > Tarvikkeet neulan tarttuja SNG-BV > VSL 6-4 PU MI-TR

Hose for vacuum and compressed-air systems



External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m


Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Suunnitteludata



Attribuutti

Arvo

d	4 mm
D	6 mm

Tekniset tiedot

Attribuutti	Arvo
Hose type	6-4
Pressure range (operating pressure)	-0.95 ... 10.00 bar
Operating temperature	-20 ... 90 °C
Bending radius min.	35 mm
Length max.	500 m
Weight/Meter	16 g/m
Weight/Meter	0,02 kg/m
Material hose	PU

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum hose (meter)

VSL 6-4 PU MI-TR

Osanro.:10.07.09.00002

<https://www.schmalz.com/10.07.09.00002>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Lisätarvikkeet



ST G1/8-AG 4 MS-ROH

Osanro.:10.08.03.00153

Thread G1: G1/8"-M

Hose diameter (rec.) d: 4 mm

Material: Brass

Surface: raw

Length L: 4 mm

Nominal diameter dn: 2,5 mm



ST M5-AG 4 MS-V

Osanro.:10.08.03.00152

Thread G1: M5-M

Hose diameter (rec.) d: 4 mm

Material: Brass

Surface: nickel plated

Length L: 3,3 mm

Nominal diameter dn: 2,2 mm



STV-GE G1/4-AG 6

Osanro.:10.08.02.00205

Thread G1: G1/4"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,2 mm

Length L: 15,2 mm

Vacuum hose (meter)

VSL 6-4 PU MI-TR

Osanro.:10.07.09.00002

<https://www.schmalz.com/10.07.09.00002>



STV-GE G1/8-AG 6

Osanro.:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,4 mm

Length L: 16,4 mm



STV-GE G1/8-AG 6 HT

Osanro.:10.08.02.00389

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

External diameter D: 11,6 mm

Length L: 19 mm



STV-GE M5-AG 6

Osanro.:10.08.02.00201

Thread G1: M5-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 9,9 mm

Length L: 18,8 mm

Vacuum hose (meter)

VSL 6-4 PU MI-TR

Osanro.:10.07.09.00002

<https://www.schmalz.com/10.07.09.00002>



STVI-GE G1/4-IG 6

Osanro.:10.08.02.00153

Thread G1: G1/4"-F

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,5 mm

Length L: 30,5 mm



STVI-GE G1/8-IG 6

Osanro.:10.08.02.00150

Thread G1: G1/8"-F

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,5 mm

Length L: 26,5 mm



STV-T G1/4-AG 6

Osanro.:10.09.02.00042

Thread G1: G1/4"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

Length L: 41 mm

Vacuum hose (meter)

VSL 6-4 PU MI-TR

Osanro.:10.07.09.00002

<https://www.schmalz.com/10.07.09.00002>



STV-T G1/8-AG 6

Osanro.:10.09.02.00040

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

Length L: 41,5 mm



STV-W G1/4-AG 6

Osanro.:10.08.02.00159

Thread G1: G1/4"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 20,2 mm



STV-W G1/8-AG 6

Osanro.:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastics

Operating temperature: °C

Length L: 20,8 mm

Vacuum hose (meter)

VSL 6-4 PU MI-TR

Osanro.:10.07.09.00002

<https://www.schmalz.com/10.07.09.00002>



STV-W G1/8-AG 6

Osanro.:10.08.02.00158

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 20,1 mm



STV-W G1/8-AG 6 HT

Osanro.:10.08.02.00391

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

Length L: 22,5 mm



STV-W M5-AG 6

Osanro.:10.08.02.00296

Pressure range (operating pressure): bar

Length L: 20,8 mm

Height H: 13 mm

Thread G1: M5-M

Vacuum hose (meter)

VSL 6-4 PU MI-TR

Osanro.:10.07.09.00002

<https://www.schmalz.com/10.07.09.00002>



STV-W M5-AG 6

Osanro.:10.08.02.00235

Thread G1: M5-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 19,7 mm



STV-W M5-AG 6 HT

Osanro.:10.08.02.00397

Thread G1: M5-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -50 ... 200 °C

Length L: 22,5 mm



STV-WF G1/4-AG 6

Osanro.:10.08.02.00169

Thread G1: G1/4"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 22,9 mm

Vacuum hose (meter)

VSL 6-4 PU MI-TR

Osanro.:10.07.09.00002

<https://www.schmalz.com/10.07.09.00002>



STV-WF G1/8-AG 6

Osanro.:10.08.02.00168

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 21,4 mm



SVB-T 6

Osanro.:10.09.02.00021

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

Length L: 42 mm