

Bellows suction cup HT1 (round)

SAB 40 HT1-60 G3/8-IG

Osanro.:10.01.06.03053

<https://www.schmalz.com/10.01.06.03053>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Imukahva lasin käsittelyyn > Bellows Suction Cups SAB HT1 (1.5 Folds) > SAB 40 HT1-60 G3/8-IG

Bellows suction cup (round) for markless handling of workpieces



Size: 40

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Nipple material: Nickel plated

Connection: G3/8-IG

Number of folds: 1,5

Suunnitteludata



Attribuutti	Arvo
dn	4 mm
D1	32 mm
Dmax(S)	45 mm
Ds	40,10 mm
G1	G3/8"-F
H	44,80 mm
LG1	9,50 mm
SW1	22 mm
Z (Stroke)	10 mm

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	38 N
Pull-off force	59 N
Lateral force	36 N
Lateral force (oily surface)	33 N
Volume	7 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Size	40

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup HT1 (round)

SAB 40 HT1-60 G3/8-IG

Osanro.:10.01.06.03053

<https://www.schmalz.com/10.01.06.03053>

Number of folds	1,50
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	45,30 g
Product family	SAB