

Bellows suction cup HT1 (round)

SAB 125 HT1-60 G1/4-AG

Osanro.:10.01.06.03065

<https://www.schmalz.com/10.01.06.03065>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Imukahva lasin käsittelyyn > Bellows Suction Cups SAB HT1 (1.5 Folds) > SAB 125 HT1-60 G1/4-AG

Bellows suction cup (round) for markless handling of workpieces



Size: 125

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

Number of folds: 1,5

Suunnitteludata



Attribuutti	Arvo
dn	6 mm
D1	94 mm
Dmax(S)	135 mm
Ds	126 mm
G1	G1/4"-M
H	67,80 mm
LG1	10 mm
SW1	22 mm
Z (Stroke)	32 mm

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	250 N
Pull-off force	558 N
Lateral force	352 N
Lateral force (oily surface)	335 N
Volume	191 cm ³
Curve radius (min) (convex)	140 mm
Hose diameter (rec.) d	9 mm
Size	125

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup HT1 (round)

SAB 125 HT1-60 G1/4-AG

Osanro.:10.01.06.03065

<https://www.schmalz.com/10.01.06.03065>

Number of folds	1,50
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	179,30 g
Product family	SAB