

Suction plate (round)

SGF-HS 150 HT1-60 FM1

Osanro.:10.01.01.13490

<https://www.schmalz.com/10.01.01.13490>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Imukahva lasin käsittelyyn > Suction Plates SGF > SGF-HS 150 HT1-60 FM1

Flat suction cup (round) for highly dynamic handling of glass



Size: 150


Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Connection: FM1

Connection: 4x8,7mm LK38,2 90°

Suunnitteludata



Attribuutti	Arvo
d2	126 mm
d3	70 mm
d5	8,70 mm
dn	14,50 mm
Dmax(S)	165 mm
Ds	148,50 mm
G2	G1/4"-F
H	31,90 mm
H5	6 mm
L2	26,50 mm
LG2	20 mm
X1	27 mm
Y1	27 mm
Z (Stroke)	7,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	1060 N
Suction force d2	730 N
Volume	119 cm ³

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Suction plate (round)

SGF-HS 150 HT1-60 FM1

Osanro.:10.01.01.13490

<https://www.schmalz.com/10.01.01.13490>

Curve radius (min) (convex)	700 mm
Hose diameter (rec.) d	9 mm
Size	150
Number of folds	0
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	360 g
Product family	SGF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



SIEB 27x1 MS-A2 100 100/65

Osanro.:10.07.01.00110



TV G1/4-AG 13

Osanro.:10.05.10.00061

Thread G1: G1/4"-M

Thread G2: G1/8"-F

Spring stroke Z: 13 mm

Suction plate (round)

SGF-HS 150 HT1-60 FM1

Osanro.:10.01.01.13490

<https://www.schmalz.com/10.01.01.13490>



PC 150

Osanro.:10.01.01.13087

Size: 150



SU 160

Osanro.:10.01.01.12438

Size: 160

Clamping range: 150.0 ... 180.0 mm

Temperature resistance: 80 °C

Varaosat



VRS-S G1/4-AG

Osanro.:10.08.06.00048

Thread G1: G1/4"-M

Material: Brass

Surface: nickel plated

Suction plate (round)

SGF-HS 150 HT1-60 FM1

Osanro.:10.01.01.13490

<https://www.schmalz.com/10.01.01.13490>



DR-SGF-HS 150 HT1-60

Osanro.:10.01.01.13176

Size: 150

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Height H: 25,9 mm