

Flat suction cup (oval)

SAOF 100x50 HT2-65 G3/8-IG

Osanro.:10.01.05.00753

<https://www.schmalz.com/10.01.05.00753>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Imukahva metallilevyn käsittelyyn > Flat Suction Cups SAOF HT2 (Oval) > SAOF 100x50 HT2-65 G3/8-IG

Flat suction cup (oval) for very dynamic handling



Dimensions (LxB): 100 x 50

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A

Nipple material: Nickel plated

Connection: G3/8-IG

Suunnitteludata



Attribuutti	Arvo
Bmax(S)	54 mm
Bs	48,10 mm
dn	8 mm
G1	G3/8"-F
H	30,50 mm
LG1	9 mm
Lmax(S)	106 mm
Ls	101,10 mm
SW1	22 mm
Z (Stroke)	5 mm

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	217 N
Lateral force	177 N
Volume	20 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	100 x 50
Connection	G3/8"-F
Number of folds	0

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (oval)

SAOF 100x50 HT2-65 G3/8-IG

Osanro.:10.01.05.00753

<https://www.schmalz.com/10.01.05.00753>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Temperature resistance	200 °C
Weight	104,40 g
Product family	SAOF