

Flat suction cup (round)

SGPN 40 NK-40 G1/8-AG

Osanro.:10.01.01.11739

<https://www.schmalz.com/10.01.01.11739>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Imukahvat folioille ja paperille > Flat Suction Cups SGPN > SGPN 40 NK-40 G1/8-AG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 40

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Suunnitteludata



Attribuutti	Arvo
dn	5 mm
Dmax(S)	42 mm
Ds	40 mm
G1	G1/8"-M
H	25,60 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	2,30 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	33 N
Volume	3,80 cm ³
Hose diameter (rec.) d	4 mm
Size	40
Number of folds	0
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	40 Shore A

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SGPN 40 NK-40 G1/8-AG

Osanro.:10.01.01.11739

<https://www.schmalz.com/10.01.01.11739>

Weight	11,10 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Varaosat



SA-NIP N035 G1/8-AG DN500

Osanro.:10.01.01.11738

Thread G1: G1/8"-M

Fitting length: 5 mm

Material: Aluminum



SGP 40 NK-40 N035

Osanro.:10.01.01.00789

Size: 40

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A