

Flat suction pad (round)

SFF 10 EPDM-45 M5-AG

Osanro.:10.01.01.14260

<https://www.schmalz.com/10.01.01.14260>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Imukahvat folioille ja paperille > Suction Cups SFF / SFB1 > SFF 10 EPDM-45 M5-AG

Flat suction cup (round) for dynamic handling of thin and flexible workpieces




Size: 10

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Suunnitteludata



Attribuutti	Arvo
Dmax(S)	11 mm
Ds	10 mm
dn	1,80 mm
G1	M5-AG
LG1	4,70 mm
H	15,40 mm
SW1	8 mm
Z (Stroke)	0,70 mm

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	2,70 N
Volume	0,25 cm ³
Size	10
Number of folds	0
Suction cup material	EPDM
Material hardness [Shore A]	45 Shore A
Weight	1,60 g
Product family	SFF

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction pad (round)

SFF 10 EPDM-45 M5-AG

Osanro.:10.01.01.14260

<https://www.schmalz.com/10.01.01.14260>

Varaosat



SFF 10 EPDM-45 SC030

Osanro.:10.01.01.14044

Size: 10

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Number of folds: 0



SC 030 M5-AG

Osanro.:10.01.06.02802

Connection geometry: 030

Connection: M5-M

Length L1: 15,5 mm

Fitting length: 5 mm

Nominal diameter dn: 1,8 mm