

Bellows suction cups (round)

SFB1 15 SI-55 G1/8-AG

Osanro.:10.01.06.04397

<https://www.schmalz.com/10.01.06.04397>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Imukahvat folioille ja paperille > Suction Cups SFF / SFB1 > SFB1 15 SI-55 G1/8-AG

Bellows suction cup (round) for very uneven workpieces flexible workpieces




Size: 15

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Suunnitteludata



Attribuutti	Arvo
Dmax(S)	16 mm
Ds	15 mm
d2	4,70 mm
dn	4,10 mm
G1	G1/8-AG
LG1	7,50 mm
H	22 mm
SW1	14 mm
Z (Stroke)	4 mm

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	1 N
Volume	0,80 cm ³
Size	15
Number of folds	1,50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Weight	5,30 g
Product family	SFB1

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cups (round)

SFB1 15 SI-55 G1/8-AG

Osanro.:10.01.06.04397

<https://www.schmalz.com/10.01.06.04397>

Varaosat



SFB1 15 SI-55 SC040

Osanro.:10.01.06.04368

Size: 15

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 1,5



SC 040 G1/8-AG

Osanro.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20,2 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm