

Flat suction cup (round)

SGAN 7 SI-55 M5-IG

Osanro.:10.01.01.00797

<https://www.schmalz.com/10.01.01.00797>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Imukahvat - monialaiset > Flat Suction Cups SGAN > SGAN 7 SI-55 M5-IG

Flat suction cup (round) for particularly sensitive workpieces



Size: 7

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Connection: M5-F

Suunnitteludata



Attribuutti	Arvo
dn	2 mm
Dmax(S)	7,50 mm
Ds	7 mm
G1	M5-F
H	22 mm
LG1	5,50 mm
SW1	8 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	1,60 N
Volume	0,19 cm ³
Curve radius (min) (convex)	7,50 mm
Hose diameter (rec.) d	2 mm
Size	7
Nipple family	N 028
Suction cup material	Silicone SI

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SGAN 7 SI-55 M5-IG

Osanro.:10.01.01.00797

<https://www.schmalz.com/10.01.01.00797>

Material hardness [Shore A]	55 Shore A
Weight	1,70 g
Number of folds	0
Product family	SGAN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Varaosat



SA-NIP N028 M5-IG DN200

Osanro.:10.01.01.00813

Thread G1: M5-F

Fitting length: 10 mm

Material: Aluminum



SGA 7 SI-55 N028

Osanro.:10.01.01.00347

Size: 7

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A