

Flat suction cup (round)

SG 16 NBR-55 N026

Osanro.:10.01.01.00195

<https://www.schmalz.com/10.01.01.00195>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Imukahvat - monialaiset > SG 16 NBR-55 N026

Flat suction cup (round)




Size: 16

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 20 mm

Suunnitteludata



Attribuutti

Arvo

d	5 mm
Dk	8 mm
Dmax(S)	17,50 mm
Ds	16 mm
H	20 mm
H2	12 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Number of folds	0
Size	16
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	8 N
Material hardness [Shore A]	55 Shore A
Product family	SG

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SG 16 NBR-55 N026

Osanro.:10.01.01.00195

<https://www.schmalz.com/10.01.01.00195>

Lisätarvikkeet



SA-NIP N026 M5-AG DN200

Osanro.:10.01.01.00319

Thread G1: M5-M

Fitting length: 3 mm

Material: Aluminum