

Bellows suction cups (round)

SPB4f 40 SI-55 G3/8-AG

Osanro.:10.01.06.03546

<https://www.schmalz.com/10.01.06.03546>

Aloitussivu > Palkeet imukuppi SPB4f (4,5-kertainen) > SPB4f 40 SI-55 G3/8-AG

Bellows suction cup (round) for very uneven workpieces



Size: 40


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Thread G1: G3/8"-M

Number of folds: 4,5

Suunnitteludata



Attribuutti

Arvo

d2	15,30 mm
dn	10,30 mm
Dmax(S)	42 mm
Ds	39,70 mm
G1	G3/8"-M
H	59,50 mm
LG1	10 mm
SW1	22 mm
Z (Stroke)	18 mm

Tekniset tiedot

Attribuutti

Arvo

Suction force at -200 mbar	6,80 N
Suction force at -400 mbar	13,60 N
Suction force (-600mbar)	20,40 N
Pull-off force	23,80 N
Volume	15,12 cm ³
Hose diameter (rec.) d	9 mm
Number of folds	4,50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cups (round)

SPB4f 40 SI-55 G3/8-AG

Osanro.:10.01.06.03546

<https://www.schmalz.com/10.01.06.03546>

Weight	26,70 g
Product family	SPB4f

Lisätarvikkeet



SIEB 17x0.8 MS-A2 103 0.103/0.07

Osanro.:10.07.01.00320

External diameter D: 17 mm

Length L: 0,8 mm

Material: Brass / Stainless steel

Filter pore size: 103 µm



SSB 16-27 ST-VZ

Osanro.:10.07.10.00002

Clamping range: 16.0 ... 27.0 mm

Material: Steel

Surface: galvanised

Varaosat

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cups (round)

SPB4f 40 SI-55 G3/8-AG

Osanro.:10.01.06.03546

<https://www.schmalz.com/10.01.06.03546>



SC 080 G3/8-AG

Osanro.:10.01.06.02593

Connection geometry: 080

Vacuum connection: G3/8"-M

Length L1: 32 mm

Fitting length: 7,5 mm

Nominal diameter dn: 10,3 mm



SPB4f 40 SI-55 SC080

Osanro.:10.01.06.03265

Size: 40

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 4,5