

Flat suction cup (round)

SUF 30 SI-55 SC040

Osanro.:10.01.01.13971

<https://www.schmalz.com/10.01.01.13971>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > SUF 30 SI-55 SC040

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 30

Suction cup material: Silicone SI

Material characteristics: FDA-compatible

Material hardness [Shore A]: 55 Shore A

Suunnitteludata



Attribuutti

Arvo

d1	10,50 mm
d	7 mm
Dk	18,60 mm
Dmax(S)	33,30 mm
Ds	30 mm
H	11,70 mm
H2	4,80 mm
H3	6,70 mm
Z (Stroke)	3 mm

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	34 N
Pull-off force	34 N
Volume	1,60 cm ³
Curve radius (min) (convex)	35 mm
Size	30
Nipple family	SC040
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Weight	4 g

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SUF 30 SI-55 SC040

Osanro.:10.01.01.13971

<https://www.schmalz.com/10.01.01.13971>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



SC 040 G1/8-AG

Osanro.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20,2 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm



SC 040 G1/8-IG

Osanro.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20,7 mm

Fitting length: 14 mm

Nominal diameter dn: 4,1 mm