

Flat suction cup (round)

PFYN 8 NBR-55 M5-AG

Osanro.:10.01.01.00139

<https://www.schmalz.com/10.01.01.00139>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > Litteä imukuppi PFYN > PFYN 8 NBR-55 M5-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 8


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: M5-M

Suunnitteludata



Attribuutti

Arvo

dn	2 mm
Dmax(S)	9 mm
Ds	8 mm
G1	M5-M
H	12 mm
LG1	4,50 mm
SW1	8 mm
Z (Stroke)	1,30 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	2,30 N
Volume	0,03 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	2 mm
Size	8
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

PFYN 8 NBR-55 M5-AG

Osanro.:10.01.01.00139

<https://www.schmalz.com/10.01.01.00139>

Weight 1,20 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Varaosat



SA-NIP N004 M5-AG DN200

Osanro.:10.01.01.03526

Thread G1: M5-M

Length L1: 13,5 mm

Fitting length: 5 mm

Material: Aluminum



PFG 8 NBR-55 N004

Osanro.:10.01.01.00009

Size: 8

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A