

Flat suction cup (round)

PFYN 2 NBR-55 M3-AG

Osanro.:10.01.01.00276

<https://www.schmalz.com/10.01.01.00276>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > Litteä imukuppi PFYN > PFYN 2 NBR-55 M3-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 2

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: M3-M

Suunnitteludata



Attribuutti	Arvo
dn	1 mm
Dmax(S)	2,50 mm
Ds	2 mm
G1	M3-M
H	6 mm
LG1	3 mm
SW1	5 mm
Z (Stroke)	0,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	0,12 N
Volume	0,00 cm ³
Curve radius (min) (convex)	2 mm
Hose diameter (rec.) d	2 mm
Size	2
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

PFYN 2 NBR-55 M3-AG

Osanro.:10.01.01.00276

<https://www.schmalz.com/10.01.01.00276>

Weight	1 g
Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Varaosat



SA-NIP N003 M3-AG DN100

Osanro.:10.01.01.00316

Thread G1: M3-M
Length L1: 7,5 mm
Fitting length: 2 mm
Material: Aluminum



PFG 2 NBR-55 N003

Osanro.:10.01.01.00003

Size: 2
Suction cup material: Nitrile rubber NBR
Material hardness [Shore A]: 55 Shore A