

Flat suction cup (round)

PFYN 15 NBR-ESD-55 G1/8-IG

Osanro.:10.01.01.14195

<https://www.schmalz.com/10.01.01.14195>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > Litteä imukuppi PFYN > PFYN 15 NBR-ESD-55 G1/8-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 15


Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-F

Suunnitteludata



Attribuutti	Arvo
dn	2 mm
Dmax(S)	17,50 mm
Ds	15 mm
G1	G1/8"-F
H	24 mm
LG1	9 mm
SW1	14 mm
Z (Stroke)	1,90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	9 N
Volume	0,40 cm ³
Curve radius (min) (convex)	12,50 mm
Hose diameter (rec.) d	4 mm
Size	15
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

PFYN 15 NBR-ESD-55 G1/8-IG

Osanro.:10.01.01.14195

<https://www.schmalz.com/10.01.01.14195>

Weight	5,80 g
Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



PFY 15 NBR-ESD-55 N005

Osanro.:10.01.01.13871

Size: 15

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A



SA-NIP N005 G1/8-IG DN200

Osanro.:10.01.01.03521

Nipple family: N 005

Thread G1: G1/8"-F

Length L1: 20,5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 2 mm

Material: Aluminum