

Suction plate (round)

SPK 250 MOS EPDM-15 G1/2-IG

Osanro.:10.01.01.12065

<https://www.schmalz.com/10.01.01.12065>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > Suction Plates SPK > SPK 250 MOS EPDM-15 G1/2-IG

Suction plate (round) for rough and structured surfaces



Size: 250


Material hardness [Shore A]: 15 Shore A

Material type: Foam rubber

Sealing material: EPDM

Connection: G1/2"-F

Suunnitteludata



Attribuutti	Arvo
d3	235 mm
Dmax(S)	269 mm
Ds	249 mm
G1	G1/2"-F
G2	G1/2"-F
H	25,50 mm
L2	76 mm
LG1	14,50 mm
LG2	14,50 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	2714 N
Volume	291 cm ³
Curve radius (min) (convex)	2600 mm
Hose diameter (rec.) d	12 mm
Size	250
Material hardness [Shore A]	15 Shore A
Weight	2310 g

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Suction plate (round)

SPK 250 MOS EPDM-15 G1/2-IG

Osanro.:10.01.01.12065

<https://www.schmalz.com/10.01.01.12065>

Number of folds	0
Product family	SPK

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



TV G1/2-AG 13

Osanro.:10.05.10.00038

Thread G1: G1/2"-M

Thread G2: G3/8"-F

Spring stroke Z: 13 mm



SU 280

Osanro.:10.01.01.12485

Size: 280

Clamping range: 270.0 ... 300.0 mm

Temperature resistance: 80 °C

Varaosat

Suction plate (round)

SPK 250 MOS EPDM-15 G1/2-IG

Osanro.:10.01.01.12065

<https://www.schmalz.com/10.01.01.12065>



DR-SPK 250 MOS EPDM-15

Osanro.:10.01.01.12077

Size: 250

Material type: Foam rubber

Material hardness [Shore A]: 15 Shore A

Sealing material: EPDM



VRS-S G1/4-AG

Osanro.:10.08.06.00048

Thread G1: G1/4"-M

Material: Brass

Surface: nickel plated



DR-SPK 250 MOS EPDM-15

Osanro.:10.01.01.12077

Size: 250

Material type: Foam rubber

Material hardness [Shore A]: 15 Shore A

Sealing material: EPDM