

Suction plate (round)

SPU 210 NBR-55 G1/2-IG AE

Osanro.:10.01.01.01151

<https://www.schmalz.com/10.01.01.01151>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > Suction Plates SPU > SPU 210 NBR-55 G1/2-IG AE

Suction plate (round), universal, for smooth and slightly rough surfaces




Size: 210

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Connection: G1/2"-F

Suunnitteludata



Attribuutti	Arvo
d	34 mm
d2	163 mm
d3	138 mm
Dmax(S)	220 mm
Ds	210 mm
G1	G1/2"-F
G2	G1/4"-F
H	25,50 mm
H1	27 mm
L2	36,50 mm
LG1	13,50 mm
LG2	15 mm
Z (Stroke)	8 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	1870 N
Suction force d2	1250 N
Volume	194 cm ³

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Sivu 1 alkaen 2

Suction plate (round)

SPU 210 NBR-55 G1/2-IG AE

Osanro.:10.01.01.01151

<https://www.schmalz.com/10.01.01.01151>

Hose diameter (rec.) d 12 mm

Size 210

Suction cup material Nitrile rubber NBR

Material hardness [Shore A] 55 Shore A

Weight 870 g

Number of folds 0

Product family SPU

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



SU 210


Osanro.:10.01.01.12439

Size: 210

Clamping range: 210.0 ... 220.0 mm

Temperature resistance: 80 °C

Varaosat



DR-SPU 210 NBR-55

Osanro.:10.01.01.01089

Size: 210

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A