

Suction plate (round)

SUF 160 NBR-60 G1/2-IG VRS

Osanro.:10.01.01.14330

<https://www.schmalz.com/10.01.01.14330>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (pyöreä) > Suction Plates SUF > SUF 160 NBR-60 G1/2-IG VRS

Suction plate (round), universal, for smooth and slightly rough surfaces




Size: 160

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

contains: Screw plug

Suunnitteludata



Attribuutti	Arvo
d2	130 mm
Dmax(S)	170 mm
Dmk	66,50 mm
Ds	160 mm
G1	G1/2"-F
G2	G1/4"-F
G3	M8-F
H	30 mm
L2	32,50 mm
LG1	14 mm
LG2	11,80 mm
LG3	11,10 mm
Z (Stroke)	9 mm

Tekniset tiedot

Attribuutti	Arvo
Product family	SUF
Size	160
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Suction plate (round)

SUF 160 NBR-60 G1/2-IG VRS

Osanro.:10.01.01.14330

<https://www.schmalz.com/10.01.01.14330>

Volume	176 cm ³
Suction force d2	790 N
Suction force (-600mbar)	1200 N
Curve radius (min) (convex)	400 mm
Hose diameter (rec.) d	12 mm
Weight	387 g

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



SIEB 27x1 MS-A2 100 100/65

Osanro.:10.07.01.00110



SIEB 15x0.8 MS-A2 0.103/0.07

Osanro.:10.07.01.00211

External diameter D: 15 mm

Length L: 0,8 mm

Material: Brass / Stainless steel

Suction plate (round)

SUF 160 NBR-60 G1/2-IG VRS

Osanro.:10.01.01.14330

<https://www.schmalz.com/10.01.01.14330>



PC 175

Osanro.:10.01.01.13088

Size: 175



TV G1/4-AG 12

Osanro.:10.05.10.00086

Thread G1: G1/4"-M

Spring stroke Z: 12 mm

Varaosat



DR-SUF 160 NBR-60

Osanro.:10.01.01.14327

Size: 160

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A