

Flat suction cup (oval)

SGON 30x10 NBR-55 G1/8-AG

Osanro.:10.01.05.00100

<https://www.schmalz.com/10.01.05.00100>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Litteä imukuppi (soikea) > Flat Suction Cups SGON > SGON 30x10 NBR-55 G1/8-AG

Flat suction cup (oval) for long and also curved workpieces



Dimensions (LxB): 30 x 10


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: G1/8"-M

Suunnitteludata



Attribuutti	Arvo
Bmax(S)	11,50 mm
Bs	9,40 mm
dn	2,50 mm
G1	G1/8"-M
H	17 mm
LG1	8 mm
Lmax(S)	30,50 mm
Ls	29,40 mm
SW1	14 mm
Z (Stroke)	1,50 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	12,20 N
Volume	0,52 cm ³
Curve radius (min) (convex)	7,50 mm
Hose diameter (rec.) d	4 mm
Dimensions (LxB)	30 x 10
Number of folds	0
Suction cup material	Nitrile rubber NBR

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (oval)

SGON 30x10 NBR-55 G1/8-AG

Osanro.:10.01.05.00100

<https://www.schmalz.com/10.01.05.00100>

Material hardness [Shore A]	55 Shore A
-----------------------------	------------

Weight	6,80 g
--------	--------

Product family	SGON
----------------	------

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Varaosat



SA-NIP N022 G1/8-AG DN350

Osanro.:10.01.05.00124

Thread G1: G1/8"-M

Length L1: 18,5 mm

Fitting length: 5 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SGO 30x10 NBR-55 N022

Osanro.:10.01.05.00152

Dimensions (LxB): 30 x 10

Suction cup material: Nitrile rubber NBR
--

Material hardness [Shore A]: 55 Shore A

Flat suction cup (oval)

SGON 30x10 NBR-55 G1/8-AG

Osanro.:10.01.05.00100

<https://www.schmalz.com/10.01.05.00100>



ZOKL 11-13

Osanro.:10.07.10.00032

Clamping range: 11.0 ... 13.0 mm

Material: Galvanized steel