

Suction plate (oval)

SPLO 300x100 NBR-55 TV

Osanro.:10.01.05.00188

<https://www.schmalz.com/10.01.05.00188>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Litteä imukuppi (soikea) > Suction Plates SPLO > SPLO 300x100 NBR-55 TV

Flat suction cup (oval) for narrow or curved workpieces




Dimensions (LxB): 300 x 100

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 25 mm

Suunnitteludata



Attribuutti	Arvo
B3	65 mm
Bk	67,70 mm
Bmax(S)	108 mm
Bs	98,80 mm
G1	G1/4"-M
G2	G1/8"-F
G3	M6-F
H	25 mm
H1	53,50 mm
L2	92 mm
L3	264 mm
LG1	13 mm
LG2	9,50 mm
LG3	9 mm
Lk	266,70 mm
Lmax(S)	308 mm
Ls	297,80 mm
X1	70 mm
Y1	40 mm
Z (Stroke)	8,80 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Suction plate (oval)

SPLO 300x100 NBR-55 TV

Osanro.:10.01.05.00188

<https://www.schmalz.com/10.01.05.00188>

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	1250 N
Volume	256,39 cm ³
Curve radius (min) (convex)	175 mm
Number of folds	0
Dimensions (LxB)	300 x 100
Suction cup material	Nitrile rubber NBR
Weight	1300 g
Product family	SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor