

Bellows suction cup (round)

FG 20 NBR-55 N016

Osanro.:10.01.06.00054

<https://www.schmalz.com/10.01.06.00054>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Palkeet imukupit (pyöreät) > FG 20 NBR-55 N016

Bellows suction cup (round) for very uneven workpieces




Size: 20

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5

Suunnitteludata



Attribuutti

Arvo

d	4,50 mm
d2	10,50 mm
D1	20 mm
Dk	10 mm
Dmax(S)	21 mm
Ds	20 mm
H	22,10 mm
H2	3,80 mm
H3	9 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	5,20 N
Pull-off force	12,10 N
Volume	2,30 cm ³
Curve radius (min) (convex)	30 mm
Size	20
Nipple family	N 016
Number of folds	2,50

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup (round)

FG 20 NBR-55 N016

Osanro.:10.01.06.00054

<https://www.schmalz.com/10.01.06.00054>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	2,40 g
Product family	FG

Lisätarvikkeet



SA-NIP N016 G1/8-AG DN350

Osanro.:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Osanro.:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

Bellows suction cup (round)

FG 20 NBR-55 N016

Osanro.:10.01.06.00054

<https://www.schmalz.com/10.01.06.00054>



SA-NIP N016 M5-AG DN250

Osanro.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Material: Aluminum