

Bellows suction cup (round)

FG 32 SI-55 N018

Osanro.:10.01.06.00144

<https://www.schmalz.com/10.01.06.00144>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Palkeet imukupit (pyöreät) > FG 32 SI-55 N018

Bellows suction cup (round) for very uneven workpieces



Size: 32


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 2,5

Suunnitteludata



Attribuutti

Arvo

d	8 mm
d1	15 mm
d2	16 mm
D1	32,40 mm
Dk	18 mm
Dmax(S)	33,50 mm
Ds	32 mm
H	37,50 mm
H2	13 mm
H3	17 mm
Z (Stroke)	15 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	12,06 N
Pull-off force	36,90 N
Volume	9,77 cm ³
Curve radius (min) (convex)	35 mm
Size	32
Nipple family	N 018

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup (round)

FG 32 SI-55 N018

Osanro.:10.01.06.00144

<https://www.schmalz.com/10.01.06.00144>

Number of folds	2,50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Weight	8,90 g
Product family	FG

Lisätarvikkeet



SA-NIP N018 G1/4-AG DN440

Osanro.:10.01.06.01065

Nipple family: N 018

Thread G1: G1/4"-M

Length L1: 28,8 mm

Fitting length: 4 mm

Nominal diameter dn: 4,4 mm

Spanner size SW2: 5 mm

Material: Aluminum



SA-NIP N018 G1/4-IG DN440

Osanro.:10.01.06.01066

Nipple family: N 018

Thread G1: G1/4"-F

Length L1: 28,8 mm

Fitting length: 15 mm

Nominal diameter dn: 4,4 mm

Spanner size SW2: 5 mm

Material: Aluminum