

Bellows suction cup (round)

FG 9 NBR-CO-55 N016

Osanro.:10.01.06.03259

<https://www.schmalz.com/10.01.06.03259>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Palkeet imukupit (pyöreät) > FG 9 NBR-CO-55 N016

Bellows suction cup (round) for very uneven workpieces




Size: 9

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5

Suunnitteludata



Attribuutti	Arvo
d	4,50 mm
d2	4,10 mm
D1	8,90 mm
Dk	9 mm
Dmax(S)	9,50 mm
Ds	9 mm
H	15 mm
H2	3,80 mm
H3	8,20 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	0,79 N
Pull-off force	2,30 N
Volume	0,30 cm ³
Curve radius (min) (convex)	10 mm
Size	9
Nipple family	N 016
Number of folds	2,50

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup (round)

FG 9 NBR-CO-55 N016

Osanro.:10.01.06.03259

<https://www.schmalz.com/10.01.06.03259>

Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A
Weight	0,60 g
Product family	FG