

Bellows suction cup SI-HD (round)

FGA 22 SI-HD-65 N016

Osanro.:10.01.06.03419

<https://www.schmalz.com/10.01.06.03419>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Imukupit > Palkeet imukupit (pyöreät) > FGA 22 SI-HD-65 N016

Bellows suction cup (round) for wear-resistant Handling surfaces



Size: 22


Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Material characteristics: FDA-compatible

Number of folds: 1,5

Suunnitteludata



Attribuutti

Arvo

d	4,50 mm
d2	11,70 mm
D1	24,20 mm
Dk	10 mm
Dmax(S)	25 mm
Ds	21,50 mm
H	19 mm
H2	3,80 mm
H3	9,10 mm
Z (Stroke)	5,30 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Number of folds	1,50
Suction force (-600mbar)	5,70 N
Size	22
Suction cup material	Silicone SI-HD
Weight	2,10 g
Curve radius (min) (convex)	10 mm
Product family	FGA

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup SI-HD (round)

FGA 22 SI-HD-65 N016

Osanro.:10.01.06.03419

<https://www.schmalz.com/10.01.06.03419>

Lisätarvikkeet



SA-NIP N016 G1/8-AG DN350

Osanro.:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Osanro.:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SA-NIP N016 M5-AG DN250

Osanro.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Material: Aluminum

Bellows suction cup SI-HD (round)

FGA 22 SI-HD-65 N016

Osanro.:10.01.06.03419

<https://www.schmalz.com/10.01.06.03419>



SA-NIP N016 G1/8-AG DN310

Osanro.:10.01.06.04062

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 M5-AG DN250

Osanro.:10.01.06.04365

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 M5-IG DN310

Osanro.:10.01.06.04689

Nipple family: N 016

Thread G1: M5-F

Length L1: 16 mm

Fitting length: 10 mm

Nominal diameter dn: 3,1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel

Bellows suction cup SI-HD (round)

FGA 22 SI-HD-65 N016

Osanro.:10.01.06.03419

<https://www.schmalz.com/10.01.06.03419>



SA-NIP N016 G1/8-IG DN310

Osanro.:10.01.06.04690

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,1 mm

Material: Aust. Stainless steel