

Bellows suction cups (round)

FSG 9 HT1-60 G1/8-IG

Osanro.:10.01.06.00978

<https://www.schmalz.com/10.01.06.00978>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Palkeet imukupit (pyöreät) > Bellows Suction Cups FSG (2.5 Folds) > FSG 9 HT1-60 G1/8-IG

Bellows suction cup (round) for very uneven workpieces



Size: 9

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A


Nipple material: Aluminum

Connection: G1/8"-F

Number of folds: 2,5

Vacuum connection: G1/8"-F

Suunnitteludata



Attribuutti	Arvo
d2	4,10 mm
dn	3,50 mm
Dmax(S)	9,50 mm
Ds	9 mm
G1	G1/8"-F
H	27 mm
LG1	8,50 mm
SW1	14 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Size	9
Number of folds	2,50
Connection	G1/8-IG
Curve radius (min) (convex)	10 mm
Volume	0,15 cm ³

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cups (round)

FSG 9 HT1-60 G1/8-IG

Osanro.:10.01.06.00978

<https://www.schmalz.com/10.01.06.00978>

Suction force (-600mbar)	0,79 N
Pull-off force	2,30 N
Hose diameter (rec.) d	4 mm
Weight	4,90 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Lisätarvikkeet



SPI 9 PEEK

Osanro.:10.01.06.03280

Size: 9

Material: Polyetheretherketon

Varaosat



SA-NIP N016 G1/8-IG DN350

Osanro.:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

Bellows suction cups (round)

FSG 9 HT1-60 G1/8-IG

Osanro.:10.01.06.00978

<https://www.schmalz.com/10.01.06.00978>



FG 9 HT1-60 N016

Osanro.:10.01.06.00878

Size: 9

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 2,5