

Compact ejector

SCP 25 FS RP

Osanro.:10.02.02.01956

<https://www.schmalz.com/10.02.02.01956>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipaineekomponentit > Tyhjiögeneraattori > Kompaktit ejektorit > Kompaktit ejektorit SCP-FS > SCP 25 FS RP

Compact ejector with integrated functions



Nozzle diameter: 2,5 mm

Suction rate (max.): 161 l/min


Air consumption suction: 310 l/min

Pressure range (operating pressure): 5.0 ... 6.0 bar

Control valve: External control

Function: pneumatic air-saving function

Suunnitteludata



Attribuutti	Arvo
B	25 mm
d	5,50 mm
G1	G1/4"-F
G2	G3/8"-F
H	77 mm
H1	150,50 mm
H2	73,50 mm
H3	20,10 mm
L	112,50 mm
L2	37,50 mm
X1	49,50 mm
X2	69,50 mm
Y1	12 mm

Tekniset tiedot

Attribuutti	Arvo
Nozzle diameter	2,50 mm
Degree of evacuation	85 %
Suction rate (max.)	161 l/min
Control valve	External control

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Compact ejector

SCP 25 FS RP

Osanro.:10.02.02.01956

<https://www.schmalz.com/10.02.02.01956>

Suction rate (max.)	5,69 cfm
Product family	SCP

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Varaosat



FILT-EINS 50 14x49 PE-POR SCP-SMP

Osanro.:10.02.02.00654

External diameter D: 13,6 mm

Length L: 48,5 mm

Filter material: Polyethylene

Construction use: Compact ejectors



SD 50.5x21x68.5 SCP-SMP25/30

Osanro.:10.02.02.01318

Pressure range (operating pressure): bar