

Vacuum pump

EVE-TR 25 AC3 IE3-TYP2 F

Osanro.:10.03.01.00353

<https://www.schmalz.com/10.03.01.00353>

Aloitussivu > Dry-Running Vacuum Pumps EVE-TR > EVE-TR 25 AC3 IE3-TYP2 F

Oil-free pump with constant suction rate, robust, requires little maintenance



Current type: three-phase current

Voltage at 60Hz: YY230/Y460V ±10%

Suction rate (60 Hz): 30 m³/h

Rated power 60 Hz: 0,9 kW


Construction: IE3:US/CAN

with: Filter

Permission: UL/CSA

Weight: 29,5 kg

Suunnitteludata



Attribuutti

Arvo

B	270 mm
B2	50 mm
d	7 mm
G2	G3/4"-F
G3	G3/4"-F
H	292 mm
H1	380 mm
H2	70 mm
L	465 mm
L2	96 mm
X1	220 mm
Y1	190 mm

Tekniset tiedot

Attribuutti	Arvo
Suction rate (60 Hz)	30 m ³ /h
Voltage at 60Hz	
Rated power 60 Hz	0,90 kW
Current type	AC3
Current type	three-phase current
Construction	IE3:US/CAN

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum pump

EVE-TR 25 AC3 IE3-TYP2 F

Osanro.:10.03.01.00353

<https://www.schmalz.com/10.03.01.00353>

Weight	29,50 kg
Protection type IP	IP 55
Product family	EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Lisätarvikkeet



VBV -950...0 G1-AG EVE 10-40

Osanro.:10.03.01.00136

External diameter D: 46 mm

Max. vacuum: -950 mbar

Thread G1: G1"-M

Length L: 53,5 mm

Construction use: Pump EVE

Size: 10-40



MSS-K 1.6-2.5A

Osanro.:10.04.04.00119

Construction use: PKZM0

Protection type IP: IP 65

Measuring range: bar

Varaosat

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum pump

EVE-TR 25 AC3 IE3-TYP2 F

Osanro.:10.03.01.00353

<https://www.schmalz.com/10.03.01.00353>



FILT-EINS 3 65x70 PAP STF-3/4-IG

Osanro.:10.07.01.00017

Filter pore size: 3 µm

External diameter D: 65 mm

Length L: 69,5 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 3/4-IG



FILT-EINS 64x71 PAP EVE-TR-25-40-50

Osanro.:10.03.01.00029

Construction use: Pump EVE-TR

Size: 25-40-50



VST EVE-TR-25

Osanro.:10.03.01.00134

Construction use: Pump EVE-TR

Size: 25

contains: Brush slide

and: Filter